























-  MONTAGEANLEITUNG
-  ASSEMBLY INSTRUCTION
-  DE INSTRUCTIE VAN DE ASSEMBLAGE
-  ISTRUZIONE DELL'ASSEMBLEA
-  INSTRUCCIÓN DE ASAMBLEA
-  INSTRUCTION DE MONTAGE
-  NÁVOD K MONTÁŽI
-  MONTERINGSANVISNING
-  MONTAJ TALIMATI
-  ASENNUSOHJE
-  BRUGSANVISNING
-  BRUKSANVISNING
-  UPUTE ZA MONTAŽU
-  NAVODILA ZA MONTAŽO
-  GYŰLÉS OKTATÁS
-  INSTRUCȚIUNI DE MONTAJ













## Art.-Nr. 70190

(70191, 70192, 70194, 70196, 70197)

2x			1200 x 200 mm
2x			200 x 600 mm
1x			180 x 600 mm
1x			180 x 600 mm
2x			375 x 560 mm
1x			400 x 560 mm


2x			400 x 595 mm
1x			400 x 595 mm
2x			390 x 140 mm
1x			100 x 90 mm
18x			130 x 100 x 50 mm

30x		M5 x 10
30x		5,3
30x		M5
6x		6 x 12
6x		
6x		6,4


3x		
3x		
4x		4,5 x 45
4x		E 6 x 30




1. – 3.



4. – 8.







9. – 13.





1.





- 2x  M5 x 10
- 2x  5,3
- 2x  M 5






PH 2 x 100

SW 8

2.






- 1x  M5 x 10
- 1x  5,3
- 1x  M 5



PH 2 x 100

SW 8

- 1x  M5 x 10
- 1x  5,3
- 1x  M 5



PH 2 x 100

SW 8









3.




PH 2 x 100





SW 8

-   M5 x 10
-   5,3
-   M 5





4.

2x



1x





5.

- 6x M5 x 10
- 6x 5,3
- 6x M 5



4x



6.




PH 2 x 100



SW 8

2x



- 4x M5 x 10

- 4x 5,3


- 4x M 5



PH 2 x 100




SW 8





7.



4x



4x



4x



PH 2 x 100



SW 8

8.

2x



8x



M5 x 10

8x



5,3

8x





M5



PH 2 x 100

SW 8



2x



M5 x 10

2x




5,3

2x






M5







9.



10.





**fix !**



PH 2 x 100



SW 8







11.



400 mm



12.




**fix !**



PH 2 x 100



SW 8



3x



3x





13.



