


DIN 935-1

Sechskant-Kronenmuttern



≤ M 10 ≥ M 12

Maße	M 4	M 5	M 6	M 8	M 10	M 12	M 14	M 16
$d_{e \max.}$	–	–	–	–	–	16	18	22
m	5	6	7,5	9,5	12	15	16	19
$n_{\min.}$	1,2	1,4	2	2,5	2,8	3,5	3,5	4,5
$s_{\text{ISO/DIN}}$	7	8	10	13	16/17	18/19	21/22	24
$w_{\max.}$	3,2	4	5	6,5	8	10	11	13
Splint	1x10	1,2x12	1,6x14	2x16	2,5x20	3,2x22	3,2x25	4x28

Maße	M 18	M 20	M 22	M 24	M 27	M 28*	M 30	M 32*
$d_{e \max.}$	25	28	32	34	38	38	42	46
m	21	22	26	27	30	30	33	35
$n_{\min.}$	4,5	4,5	5,5	5,5	5,5	5,5	7	7
$s_{\text{ISO/DIN}}$	27	30	34/32	36	41	41	46	50
$w_{\max.}$	15	16	18	19	22	22	24	26
Splint	4x32	4x36	5x36	5x40	5x45	5x50	6,3x50	6,3x56