


Allgebrauchslampen in Sonderspannungen, stossfest

Socket E27

(60 x 105 mm)

| Spannung | Leistung | Ausf. | Artikel-Nr. | EEK | EAN 4021553.... |
|-------------------------------|----------|----------|-------------|--------|--------------------|
| 130V 74x133mm 80x156mm | 15W | matt | NL13015M | | 522180 |
| | 25W | matt | NL13025M | | 522197 |
| | 25W | klar | NL13025K | | 524511 |
| | 40W | matt | NL13040M | | 522203 |
| | 40W | klar | NL13040K | | 522296 |
| | 60W | matt | NL13060M | | 522210 |
| | 60W | klar | NL13060K | | 522654 |
| | 100W | matt | NL13010M | | 522395 |
| | 100W | klar | NL13010K | | 524184 |
| 240V | 200W | matt | NL13020M | | 522838 |
| | 200W | klar | NL13020K | | 522845 |
| 240V | 8W | matt | NL24008M | E | 522630 |
| 260V 80x155mm | 200W | klar | NL23020SK | E | 522920 |
| | 200W | matt | NL23020SM | E | 522913 |
| 260V longlife Stossfest | 15W | matt | NL26015M | E | 522302 |
| | 15W | klar | NL26015K | E | 522357 |
| | 25W | matt | NL26025M | E | 52219 |
| | 25W | klar | NL26025K | E | 522364 |
| | 40W | matt | NL26040M | E | 522326 |
| | 40W | klar | NL26040K | E | 522371 |
| | 60W | matt | NL26060M | E | 522333 |
| | 60W | klar | NL26060K | E | 522388 |
| | 100W | matt | NL26010M | E | 522340 |
| 100W | klar | NL26010K | E | 522395 | |



AGL

Allgebrauchslampen in Netzspannung, longlife, stossfest

Socket E27

(60 x 105 mm)

| Spannung | Ausf. | Leistung | Artikel | EEK | EAN 4021553.... |
|----------|-------|----------|----------|-----|--------------------|
| 235V | klar | 15W | NL23615K | E | 524443 |
| | klar | 25W | NL23625K | E | 524290 |
| | matt | 25W | NL23625M | E | 524344 |
| | klar | 40W | NL23640K | E | 524306 |
| | matt | 40W | NL23640M | E | 524351 |
| | klar | 60W | NL23660K | E | 524313 |
| | matt | 60W | NL23660M | E | 524368 |
| | klar | 100W | NL23610K | E | 524320 |
| | matt | 100W | NL23610M | E | 524375 |

