



Waagrecht und senkrecht
einsetzbar
Horizontal and vertical use

Typ „Picco“

PTC Heizung / PTC Heating

Ausführungen / Performances:

Leistungen Power	Spannungen Voltage	Maße Dimension	Anschluss Connection	Artikel Nr. // Art. No. <i>ohne Lüfter / without fan</i>
15 W	110-265 V AC/DC	X	Kabel / Cable 2x0,75mm ²	01401520Kb0
20 W	110-265 V AC/DC	73x40x47mm	Kabel / Cable 2x0,75mm ²	01402020Kb0
50 W	110-265 V AC/DC	102x40x47mm	Kabel / Cable 2x0,75mm ²	01405020Kb0
70 W	110-265 V AC/DC	102x40x47mm	Kabel / Cable 2x0,75mm ²	01407020Kb0
15 W	10-60 V AC/DC	73x40x47mm	Kabel / Cable 2x0,75mm ²	01401510Kb0
20 W	10-60 V AC/DC	73x40x47mm	Kabel / Cable 2x0,75mm ²	01402010Kb0
50 W	10-60 V AC/DC	102x40x47mm	Kabel / Cable 2x0,75mm ²	01405010Kb0
70 W	10-60 V AC/DC	102x40x47mm	Kabel / Cable 2x0,75mm ²	01407010Kb0

Montage / mounting: Clip für DIN Hutschiene EN 60715
clip for DIN rail EN 60715

wahlweise Schraubbefestigung
optional screw fixing

Anschlussplan / Connection:

