



TS-231P2



HARDWARESPEZIFIKATIONEN

SOFTWARESPEZIFIKATIONEN

LIEFERUMFANG

Ordering P/N	TS-231P2-1G	TS-231P2-4G
<b>CPU</b>	Annapurna Labs AL-314, 4-core,1.7GHz	
<b>System Memory</b>	1GB DDR3 RAM	4GB DDR3 RAM
<b>RAM slot</b>	1 x SODIMM (Max. 8GB)	
<b>Flash Memory</b>	512MB NAND flash	
<b>Hard Drive Tray</b>	2	
<b>Drive Interface</b>	SATA 6Gb/s, 3Gb/s HDD or SSD; Hot-swappable	
<b>USB</b>	3 x USB 3.0 port (Front x1; Rear x 2)	
<b>LAN Port</b>	2 x GbE RJ45	
<b>LED Indicators</b>	System Status, HDD, USB, LAN	
<b>Buttons</b>	Power, Reset, USB One-Touch-Copy	
<b>System Warning</b>	Buzzer	
<b>Form Factor</b>	Tower	
<b>Dimensions</b>	169 x 102 x 219 mm 6.65 x 4.02 x 8.62 inch	
<b>Weight</b>	1.28kg (2.82 lbs)/ 2.32kg (5.11 lbs)	
<b>Power Consumption (W)</b>	HDD standby: 8.81W In operation: 23.66W	
<b>Temperature</b>	0-40 °C	
<b>Relative Humidity</b>	5~95% non-condensing, wet bulb: 27 °C	
<b>Power Supply</b>	AC adapter, 65W, 100 - 240V	
<b>Sound Level</b>	Operating Low speed: 19.2 dB(A)	
<b>Security Design</b>	Kensington security slot	
<b>Fan</b>	1 x 7cm smart Fan (12V DC)	

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use identical specifications.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting.