



NHA1112506

Output dv/dt filters _____ VW3A5301 ... 07
Metal kit IP21 ——— VW3A53902...903, VW3A53905


VW3A5301, VW3A5302,
VW3A5303, VW3A5304,
VW3A5305



VW3A53902
VW3A53903
VW3A53905



VW3A5306
VW3A5307



⚠ ⚠ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH

- Only appropriately trained persons who are familiar with and fully understand the contents of the present manual and all other pertinent product documentation and who have received all necessary training to recognize and avoid hazards involved are authorized to work on and with this equipment.
- Installation, adjustment, repair, and maintenance must be performed by qualified personnel.
- Verify compliance with all local and national electrical code requirements as well as all other applicable regulations with respect to grounding of all equipment.
- Before performing work and/or applying voltage on the equipment, follow the instructions given in the appropriate installation manual.

Failure to follow these instructions will result in death or serious injury.

⚠ CAUTION



SHARP EDGES

Use all necessary personal protective equipment (PPE) such as gloves when performing any type of work whatsoever on or with this product.


Failure to follow these instructions can result in injury or equipment damage.




Schneider Electric Limited
Stafford Park 5
Telford, TF3 3BL, UK

Electrical equipment should be installed, operated, serviced, and maintained only by qualified personnel. No responsibility is assumed by Schneider Electric for any consequences arising out of the use of this product.
© 2023 Schneider Electric. All Rights Reserved.


OUTPUT DV/DT FILTERS		METAL KIT IP21
VW3A5301	6A	VW3A53902
VW3A5302	15A	VW3A53902
VW3A5303	25A	VW3A53902
VW3A5304	50A	VW3A53903
VW3A5305	95A	VW3A53905
VW3A5306	180A	-
VW3A5307	305A	-




VW3A5301
VW3A5302
VW3A5303
VW3A5304
VW3A5305



VW3A5301 + VW3A53902
VW3A5302 + VW3A53902
VW3A5303 + VW3A53902
VW3A5304 + VW3A53903
VW3A5305 + VW3A53905






OUTPUT DV/DT FILTERS	A		B		C		D		A1		B1		Ø	
	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in
VW3A5301 + VW3A53902	295	11.6	525	20.7	215	8.5	535	21.1	210	8.3	411	16.2	7	0.28
VW3A5302 + VW3A53902	295	11.6	525	20.7	215	8.5	535	21.1	210	8.3	411	16.2	7	0.28
VW3A5303 + VW3A53902	295	11.6	525	20.7	215	8.5	535	21.1	210	8.3	411	16.2	7	0.28
VW3A5304 + VW3A53903	300	11.8	545	21.5	245	9.6	560	22.0	210	8.3	411	16.2	7	0.28
VW3A5305 + VW3A53905	300	11.8	590	23.2	245	9.6	610	24.0	210	8.3	411	16.2	7	0.28




OUTPUT DV/DT FILTERS	A		B		C		A1		B1		Ø	
	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in
VW3A5306	380	15.0	350	13.8	235	9.3	325	12.8	91	3.6	11	0.43
VW3A5307	420	16.5	360	14.2	270	10.6	360	14.2	116	4.6	11	0.43


VW3A5301, VW3A5302,
VW3A5303, VW3A5304,
VW3A5305




VW3A5306, VW3A5307



1




2







	N.m	in-lb
VW3A5301 ... 03	1.45	13
VW3A5304	2.82	25
VW3A5305	4.52	40

3






4







	N.m	in-lb
VW3A5301 ... 03	1.45	13
VW3A5304	2.82	25
VW3A5305	4.52	40




1



2



4



3

