

Logitech MX Ergo S

Marke : Logitech

Artikel-Code: 910-007260

Produktname : MX Ergo S

MX Ergo S Moderner Kabelloser Trackball
Logitech MX Ergo S. Formfaktor: rechts, Vertikale Ausführung. Bewegungserfassungs Technologie: Optisch, Geräteschnittstelle: RF Wireless + Bluetooth, Bewegung Auflösung: 2048 DPI, Tastentyp: Gedrückte Tasten, Knopfanzahl: 8, Scroll Typ: Trackball/Rad, Beschleunigung (Max.): 10 G. Energiequelle: Batterien



Maus		Energie	
Anzahl der Scroll-Rollen	1	Energiequelle *	Batterien
Scroll-Richtungen	Senkrecht	Wiederaufladbar	✓
Zweck *	Büro	Anzahl unterstützter Akkus/Batterien	1
Übertragungstechnik *	Kabellos	Akku-/Batterietyp	Integrierte Batterie
Geräteschnittstelle *	RF Wireless + Bluetooth	Akku-/Batterietechnologie	Lithium
Bewegungserfassungs Technologie *	Optisch	Akku-/Batteriekapazität	500 mAh
Bewegung Auflösung *	2048 DPI	Akku-/Batteriebetriebsdauer	500 h
Tastentyp	Gedrückte Tasten	Akkuladezeit	2 h
Scroll Typ *	Trackball/Rad	Lebensdauer der Batterie	18 Monat(e)
Programmierbare Mausknöpfe	✓	Energieverbrauch	500 mA
Knopfanzahl *	8	USB Typ-C Ladeport *	✓
Anzahl der programmierbaren Tasten	6	Gewicht und Abmessungen	
Tastenhaltbarkeit (Millionen Klicks)	3	Breite	99,8 mm
Maus-Tracking-Geschwindigkeit	20 ips	Tiefe	51,4 mm
Beschleunigung (Max.)	10 G	Höhe	132,5 mm
Stimmabgabe Rate	88,125,133 Hz	Gewicht	259 g
Frequenzband	2.4 GHz	Verpackungsdaten	
Bluetooth-Version	5.2	Menge pro Packung *	1 Stück(e)
Sensor-Typ	TCOB	Verpackungsbreite	110,1 mm
Design		Verpackungstiefe	79 mm
Formfaktor *	rechts	Verpackungshöhe	143 mm
Intelligentes, ergonomisches Design	✓	Paketgewicht	393 g
Vertikale Ausführung	✓	Verpackungsart	Box
Oberflächenfärbung	Einfarbig	Lieferumfang	
Material	Acrylnitril-Butadien-Styrol (ABS), Metall, Kunststoff, Gummi	Receiver enthalten	✓
LED-Anzeigen	✓	Kabelloser Receiver-Anschluss	USB Typ-A
		Receiver Typus	Nano-Empfänger
		Benutzerhandbuch	✓

Sonstige Funktionen

Prozessor	Nordic NRF52820
Garantiezeit	2 Jahr(e)



5099206124547

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 06-MAY-2025. Prints or copies of Information are only valid on the printed Publication date