




Mechanical characteristics

interface dimensions acc. to insertion and withdrawal force maximum permissible torque for the locking screws (4x):

Components

center contact
contact parts housing
locking screws
other metal parts
insulator

Electrical characteristics

voltage proof
contact resistance

Environmental

operating temp.
RoHS compliant

Mechanische Eigenschaften

Steckgesicht nach IEC 60169-8
Steck- und Ziehkraft
maximal zulässiges Anzugsmoment
der Verschlusschrauben (4x):

Bauteile

Innenkontakt
Kontaktteile Gehäuse
Verschlusschrauben
sonstige Metallteile
Isolierung

Elektrische Eigenschaften

Prüfspannung
Durchgangswiderstand

Umgebung

Betriebstemperatur
RoHS konform

IEC 60169-8
min.: 6 N ; max.: 15 N


0,6 Nm

Materials / Material Finish / Oberfläche

CuZn39Pb3 Ni2Au0,8
CuZn39Pb3 Ag3
CuZn39Pb3 Ni2
CuZn39Pb3 Cu2Ni5
PTFE

2 kV
≤ 5 mΩ

-20°C / +100°C
2011/65/EU

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	Datum/ date	Name/ name	Gewicht/ weight [g]			
			gez./ drawn	06.07.2020	MA				
			gepr./ appr.	06.07.2020	BJ	ca./approx. 54			
			Maßstab/ scale 2:1	Benennung/ title BNC Empty Box (m-f) BNC-Leergehäuse (m-f)				 Telegärtner	
			untel. Maße/ dim. without tolerances according to K	Untert./ doc. type		Zeichnungsnr./ drawing no. J01008C0807			 Maße/ dimensions: mm Original : DIN A4 Blatt/ sheet 1 von/ of 1
				Ersatz für/ replaces					