




USER MANUAL



i3E EOS

Thank you for purchasing the Olight product! Please read this manual carefully before using the product.

INSIDE THE BOX


i3E EOS(with Battery), User Manual.

OPERATION INSTRUCTION:

Before your first use, unscrew the light head. Remove the insulating film inside the light head before putting the light head back on.

AVAILABLE BATTERIES

- AAA Alkaline(included)
- NiMH / L92



HOW TO OPERATE

ON/OFF: Fully tighten the tailcap clockwise on the flashlight to turn the light on. Twist the tailcap counter-clockwise to turn off the light.

CAUTION: Do not insert the battery the wrong way. take out the battery if you are storing the flashlight for a long period of time to prevent the battery from leaking.

SPECIFICATIONS

SPECIFICATIONS	DETAILS
LUMENS	90 Lumens
RUNTIME	Alkaline 45minutes NiMH 70minutes
CANDELA	500 Cd
THROW	44m(144ft)
IMPACT RESISTANCE	1.5m
DIMENSIONS	(L)60.5 x (D)14mm
WEIGHT	19.4g (included battery)

Note: Tests performed with one GreenMax AAA Alkaline or eneloop pro NiMH Battery (900mAh)



WARNING

- Ensure battery is inserted with the positive (+) end pointing to the head of i3E EOS
- Do NOT throw the light directly into human eyes. This may cause temporary blindness, or permanent damage to the eyes.

WARRANTY

Within 30 days of purchase: Return to the original seller for repair or replacement.

Within 5 years of purchase: Return to Olight for repair or replacement.

Battery Warranty: Olight offers a one year warranty for all rechargeable batteries.

This warranty does not cover normal wear and tear, modifications, misuse, disintegrations, negligence, accidents, improper maintenance, or repair by anyone other than an Authorized retailer or Olight itself.

EU-DECLARATION OF CONFORMITY



EU-Declaration of Conformity can be found here CE:
<https://olightworld.com/ec-declaration>

USA Customer Support

cs@olightstore.com

Global Customer Support

Customer-service@olightworld.com

Visit **www.olightworld.com** to see our complete product line of portable illumination tools.



Olight Technology Co., Limited

Address: 5th Floor, Building A2, Fuhai Information Harbor, Fuhai Subdistrict, Bao'an District, Shenzhen, China 518103
Made In China



V1. 09, 15, 2018



3.0404.6010.9000