

Krups SA401L Vollautomatisch Espressomaschine

Marke : Krups

Artikel-Code: SA401LE0

Produktname : SA401L

Krups SA401L. Produkttyp: Espressomaschine, Kaffeezubereitungstyp: Vollautomatisch, Kaffee-Einfüllart: Kaffeebohnen, Behälter für gebrühten Kaffee: Tasse, Kapazität (in Tassen): 1 Tassen, Eingebautes Mahlwerk. Produktfarbe: Grün



Leistungen		Ergonomie	
Kaffeezubereitungstyp *	Vollautomatisch	Eingebautes Display *	✗
Behälter für gebrühten Kaffee *	Tasse	Produktfarbe *	Grün
Kapazität (in Tassen) *	1 Tassen	Energie	
Maximaler Betriebsdruck	15 bar	AC Eingangsspannung	220 - 240 V
Eingebautes Mahlwerk *	✓	AC Eingangsfrequenz	50/60 Hz
Anzahl der Mahloptionen	3	Gewicht und Abmessungen	
Einstellbare Stärke des Kaffees *	✓	Breite	150 mm
Geräteplatzierung *	Arbeitsplatte	Tiefe	295 mm
Produkttyp *	Espressomaschine	Höhe	360 mm
Kaffee-Einfüllart *	Kaffeebohnen	Gewicht	4 kg
Ursprungsland	China	Verpackungsdaten	
Kochfunktionen und -programme		Verpackungsbreite	185 mm
Espressozubereitung *	✓	Verpackungstiefe	385 mm
Zubereitung von Caffè Lungo	✓	Verpackungshöhe	410 mm
		Paketgewicht	6,5 kg



3016661181597

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity. Automated scraping, data mining, or harvesting for the purpose of training machine learning models, neural networks, or artificial intelligence systems is strictly prohibited without a commercial license.