

# KERN TC1250-0.1FN.

Ihr täglicher Begleiter - kompakt und einfach in der Handhabung

**KERN**<sup>®</sup>



## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	750 g
Net weight:	81 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Overall dimensions mounted (WxDxH):	131 x 65 x 28 mm

## Measuring system

Measuring range [Max]:	100 x 1250 µm
Precision (of [Max]):	3 %
Precision (Offset-Accur):	1 %
Readout [d]:	0 x 0,001 mm
Smallest sample surface, convex (radius):	1,500 mm
Smallest sample surface, flat (radius):	6 mm
Smallest sample surface, concave (radius):	2,500 cm
Weighing units:	µm inch (mil)

## Display

Display digit height:	1 cm
-----------------------	------

## Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

## Power supply

Operating time:	50 h
-----------------	------

## Service

ISO calibration certificate:	961-112
------------------------------	---------

## Category

Brand:	Sauter
Category:	Coating thickness
Product Group:	Coating thickness gauge