

KERN KB 2400-2N

Compact precision balance with large weighing range, as well as EC type approval [M]



Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
n/a:	20 g
Readout [d]:	10 mg
Recommended adjusting weight:	2 kg (F1)
Reproducibility:	10 mg
Resolution:	240000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	2,400 kg
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn kg lb mo oz t tl (Cn) tl (HK) tl (Singap. Malays) tl (Tw) to

Display

Display digit height:	9 mm
-----------------------	------

Counting

Counting resolution:	240000
Minimum piece weight at piece counting (Laboratory):	10 mg
Minimum piece weight at piece counting (Normal):	100 mg

Functions

Conversion function:	yes
Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	238 x 357 x 180 mm
Gross weight:	2,200 kg
Net weight:	1,500 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	167 x 250 x 85 mm
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	167 x 250 x 85 mm
Weighing surface (WxD):	130 x 130 mm