

## FISHING SCALE - "124149" - "OCS-20A"



### Standard Features:

- Strain Gauge Precision Technology
- Display Modes: kg/lb/oz
- Capacity: 30kg
- Accuracy: 20g
- Tolerance:  $\pm 20g$
- Tare Full Capacity
- Low Battery Indication / Overload Indication
- Auto-Off Function
- Material Details (Out Casing): Alloy-Aluminum
- Dimensions (LxWxH): 100x54x22mm
- Power Requirements: 2x3V CR2032
- Temperature Measure
- Tape Measure

### Packaging Details:

<b>Small Box</b>	10PCS	<b>Qty/CTN</b>	80PCS
<b>N.W.</b>	14.4kg	<b>G.W</b>	19.5kg
<b>Meas</b>	420x287x401mm		