

KERN IFB 150K20DM

Plattformwaage in schwerer Ausführung mit Eichzulassung [M], jetzt auch bis [Max] 600 kg



Measuring system

Adjustment options:	External calibration
Linearity:	20 g 50 g
Readout [d]:	20 g 50 g
Recommended adjusting weight:	150 kg (M1)
Reproducibility:	20 g 50 g
Resolution:	3 3.000
Stabilisation time:	2 s
Tare range:	-150000000 mg
Warm up time:	10 min 10 min
Weighing range [Max]:	60 kg 150 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	5,200 cm
-----------------------	----------

Technical data about verification

Minimum load [Min]:	400 g 1000 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	20 g 50 g

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	5 g
Minimum piece weight at piece counting (Normal):	50 g

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	555 x 930 x 215 mm
Gross weight:	16,350 kg
Net weight:	13,300 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Casing material:	Plastic
Dimensions of display device (WxDxH):	250 x 160 x 60 mm

KERN IFB 150K20DM



Plattformwaage in schwerer Ausführung mit Eichzulassung [M], jetzt auch bis [Max] 600 kg

Dimensions of weighing plate (WxDxH):	500 x 400 x 137 mm
of stand:	60 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	660 x 400 x 760 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	500 x 400 mm