

Measuremeter® REVOLUTION

5500E | 5505E | 5500 | 5505

With many unique features the Measure Meter and the Measuremeter Revolution should be the first choice for all your distance measuring applications. Fitted with a 1 metre circumference wheel. You have the option of electronic or mechanical versions.



Description 5500E | 5505E

The new digital Measuremeter Revolution from Trumeter, combines advanced and patented technology for the first time to a measuring wheel at costs previously unimaginable. Using the latest electronic design technology, Trumeter have manufactured an electronic distance measuring wheel with more features than ever before.

Features

- Large LCD display
- Crystal clear in direct sunlight
- Backlight for low light conditions
- Waterproof to 1 metre
- Minimum 5 year battery life
- 3 year Guarantee
- Two measuring modes; trip and total
- Pushbutton reset
- Electronic brake
- Telescopic handle
- Mud scraper
- Retractable Stand
- Adds forward subtracts in reverse.
- Accuracy $\pm 1\%$

Ordering Information

Measuremeter Revolution	
5500E	Single (metric)
5505E*	Single (imperial & metric)
5500-6E	Master carton of 6 (metric)
5505-6E*	Master carton of 6 (imperial & metric)
100712-01	Carry Bag

* Only available in USA or Canada or upon request.

- Calibration Certificate

• Model shown 5505E



Description 5500 | 5505

With many unique features the Measure Meter should be the first choice for all your distance measuring applications. Fitted with a 1 metre circumference wheel.

Features

- Large easy to read display.
- Pointer indicates start position.
- Robust construction.
- Lifetime Guarantee.
- Retractable stand.
- Telescopic handle for easy carriage.
- Adds forward subtracts in reverse.
- Imperial version measures up to 10,000 feet
- Metric version measures up to 10,000 metres
- Accuracy $\pm 1\%$

Ordering Information

Measure Meter	
5500	Single (metric)
5505	Single (imperial)
5500-6	Master carton of 6 (metric)
5505-6	Master carton of 6 (imperial)
100712-01	Carry Bag

- Calibration Certificate



MINI MEASURE REVOLUTION

5600E | 5605E | 5600 | 5605

With many unique features the Mini Measure Maxx and the Mini Measure Revolution should be the first choice for all your internal distance measuring applications. Fitted with a 25cm circumference wheel. You have the option of electronic or mechanical versions.



Description 5600E | 5605E

The new digital Mini Measure Revolution from Trumeter, combines advanced and patented technology for the first time to a measuring wheel at costs previously unimaginable. Using the latest electronic design technology, Trumeter have manufactured an electronic distance measuring wheel with more features than ever before.

The onboard microprocessor has the ability to apply mathematical calculations to the reading, making it capable of converting metres to yards or feet and inches at the push of a button. This feature is only available on the Imperial & Metric version.

Features

- Large LCD display
- Crystal clear in direct sunlight
- Backlight for low light conditions
- Weather and moisture proof
- Minimum 5 year battery life
- 3 year Guarantee
- Two measuring modes; trip and total
- Pushbutton reset
- Electronic brake
- Telescopic handle
- Adds forward subtracts in reverse

Ordering Information

Mini Measure Revolution	
5600E	Single (metric)
5605E*	Single (imperial & metric)
5600-12E	Master carton of 12 (metric)
5605-12E*	Master carton of 12 (imperial & metric)

* Only available in USA or Canada or upon request.

Description 5600 | 5605

With many unique features the Mini Measure Maxx should be the first choice for all your internal distance measuring applications. Ideal for flooring contractors, carpet fitters and many more applications.

Features

- Large 5 digit counter resets to zero.
- Imperial model: 10,000ft/inches
- Metric model: 10,000m/cm
- Lifetime Guarantee.
- Telescopic handle
- Adds forward, subtracts in reverse.

Ordering Information

Mini Measure Maxx	
5600	Single (metric)
5600-12	Master carton of 12 (metric)
5605	Single (imperial)
5605-12	Master carton of 12 (imperial)

