

BJZ	Technical Data Sheet	Order-no.: C-198 152 + C-198 166 + C-204 33216 Page 1 von 1
Description:	ESD-floormaterial <b>Safe-STAT</b>	Date: 25.10.2001

## ESD-Floormaterial **Safe-STAT**

Hardness:	80 ± 5
Thickness:	3,5 mm (C-198 152; C-198 166) 2,5 mm (C-204 33216)
Material:	Two layer synthetic rubber
Indentation behaviour:	≤ 0,30 mm
Scuff resistance:	≤ 160 mm <sup>3</sup>
Permanence of size:	no important modification
Thermal resistance:	0,025 M <sup>2</sup> °K/W
Resistance to ground:	≥ 10 <sup>10</sup> Ohm
Chemical resistance:	resistant to chemical cleaners, usually used to care
Sound insulation:	18 dB
Electrostatic behaviour by walking test:	antistatic
Resistance to slide:	≥ 1 (coefficient μ)
Effect with glowing tobacco products:	no burning on surface
Behaviour in fire:	M 3