

**HT03087**  
**ANTISTATIC SERVICE KIT WITH POCKET**  
**60 x 60 cm BLACK**

**A.**

Material is 0.37 mm thick, red static dissipative vinyl.  
Surface resistance on both sides is  $10e8 - 10e10$  Ohms, per ANSI EOS/-S4.1.

**B.**

With pocket sewn into the work surface provide storage for the tools or components.

**C.**

One ground snap, 10 mm male, permanently riveted to the material.

**D.**

Item include kits:

1. Static dissipative work surface with pocket (60 x 60 cm)
2. One antistatic brush.
3. One antistatic elastic wrist strap.
4. One 300 cm connect coil cord, two end 10 mm female snap.
5. One 300 cm straight cord with male/female (stackable) snap termination one end, banana jack & alligator clip at another end.

**E.**

The grounding cords are complete with a 1 meg. ohm resistor.

**Specification:**

Color	Black
Thickness	0.37 mm

**Electrical properties:**

Surface resistivity  $10e8 - 10e10$  Ohm/sq per ASTM-D257