

**Industrial Ethernet
IE-FM5Z2VO0005MLD0LD0X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, LC duplex - LC duplex, orange, Core diameter 50 µm

General ordering data

Type	IE-FM5Z2VO0005MLD0LD0X
Order No.	1062550000
Version	Pre-assembled patch cable, crossover, LC-Duplex IP 20, LC-Duplex IP 20, 50 µm, PVC, 5 m
GTIN (EAN)	4032248813254
Qty.	1 pc(s).

**Industrial Ethernet
IE-FM5Z2V00005MLD0LD0X**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	5 m	Net weight	120 g
--------	-----	------------	-------

Temperatures

Operating temperature	-5 °C...+75 °C	Storage temperature	-25 °C...+75 °C
Installation temperature	-5 °C...+50 °C		

Standards

Connector standard	IEC 61754-20
--------------------	--------------

Fibre-optic

Attenuation	≤ 2.7 dB/km at 850 nm, ≤ 0.7 dB/km at 1300 nm	Bandwidth	≥ 600 MHz*km at 850 nm, ≥ 1200 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM2		

Cable structure

Core diameter	50 µm	Sheath diameter	3*6 mm
Cable layout	ZIPCORD	Standard designations	I-V(ZN)Y
Material sheath	PVC	Sheathing colour	Orange

Mechanical and material properties of cable

Min. bending radius, once only	30 mm	Min. bending radius, repetitive	60 mm
--------------------------------	-------	---------------------------------	-------

plug

Version connector left	LC-Duplex IP 20	Version connector right	LC-Duplex IP 20
------------------------	-----------------	-------------------------	-----------------

Classifications

ETIM 3.0	EC000034	UNSPSC	30-21-18-01
eClass 5.1	27-06-18-03	eClass 6.2	27-08-10-03
eClass 7.1	27-08-10-03		

Approvals

Approvals



ROHS	Conform
------	---------

Datenblatt

**Industrial Ethernet
IE-FM5Z2V00005MLD0LD0X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Detailed drawing

