

**FBK
FBK 40/200 RK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

The pre-assembled control cables have pluggable 10- or 40-pole socket blocks according to IEC 603/1 DIN 41 651. They can be used to connect the PLC front adapter to the active or passive Weidmüller interfaces. They are available in different lengths.

General ordering data

Type	FBK 40/200 RK
Order No.	8216370000
Version	Pre-assembled cable, FBK, FLAT CABLE PLANO HE10 40P
GTIN (EAN)	4008190263584
Qty.	1 pc(s).

Data sheet

**FBK
FBK 40/200 RK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 329 g

Temperatures

Storage temperature, max.	70 °C	Storage temperature, min.	-10 °C
Operating temperature		Storage temperature	-10...70 °C

General Data

Connector PLC side	FLAT CABLE PLANO HE10 40P	Interface connector	FLAT CABLE PLANO HE10 40P
Number of poles, min.	40-pole	Cable	Cable LiYY
Cable length	2 m	Material	PVC
Wire cross-section	0.14 mm ²		

Electrical Data

Rated voltage (text)	< 50 V AC, ≤ 50 V DC	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	55 mΩ/m

Classifications

ETIM 3.0	EC000237	ETIM 4.0	EC000237
ETIM 5.0	EC000237	ETIM 6.0	EC000237
UNSPSC	26-12-16-03	eClass 5.1	27-24-22-14
eClass 6.2	27-24-92-05	eClass 7.1	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

Approvals

Approvals



ROHS Conform