

RSD
Diodenbox 8 Di 3A 1600V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Interfaces with diodes for surge voltage protection, lamp testing or protection against reversed polarity.

General ordering data

Type	Diodenbox 8 Di 3A 1600V
Order No.	8943110000
Version	Interface, RSD
GTIN (EAN)	4032248752300
Qty.	1 pc(s).

RSD
Diodenbox 8 Di 3A 1600V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	125 mm	Length (inches)	4.921 inch
Width	55.5 mm	Width (inches)	2.185 inch
Height	100 mm	Height (inches)	3.937 inch
Net weight	430 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-25 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-40 °C
Operating temperature	-25...70 °C	Ambient temperature	+70°C
Storage temperature	-40...70 °C		

Connection data

Type of connection	Tension-clamp connection	Type of component	Diode
--------------------	--------------------------	-------------------	-------

Rating Data

Rated current per connection	3 A
------------------------------	-----

Insulation coordination

Pollution severity level	2
--------------------------	---

Connection field

Type of connection	Tension-clamp connection	Clamping range, min.	0.08 mm ²
Clamping range, max.	1 mm ²	Stripping length	7 mm

Classifications

ETIM 4.0	EC001421	ETIM 5.0	EC001421
ETIM 6.0	EC000677	eClass 6.2	25-13-90-90
eClass 7.1	27-14-11-52	eClass 8.1	27-14-11-52
eClass 9.0	27-14-31-10	eClass 9.1	27-21-03-01

Approvals

ROHS	Conform
------	---------