

FLECAFIX 11/24**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Screwing tool for fixing and loosening cable glands and accessories in the sizes 11-36 AF.

- Can reach over several rows of glands
- No deforming of the cable glands
- Spanner size 11 to 36 mm
- Infinite adjustment of spanner size
- Ratchet function: not necessary to remove tool between turns
- Authentic one-hand tool

General ordering data

Type	FLECAFIX 11/24
Order No.	9015900000
Version	Tools, Cable gland tool
GTIN (EAN)	4032248309573
Qty.	1 pc(s).

FLECAFIX 11/24

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	190 mm	Width (inches)	7.48 inch
Height	60 mm	Height (inches)	2.362 inch
Depth	30 mm	Depth (inches)	1.181 inch
Weight	190 g	Net weight	172.9 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Screwing tools

Size	11 - 24 mm
------	------------

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC000149
UNSPSC	27-11-17-02	eClass 5.1	21-04-01-90
eClass 6.2	21-04-01-90	eClass 7.1	21-04-01-90
eClass 8.1	21-04-01-90	eClass 9.0	21-04-50-03
eClass 9.1	21-01-90-90		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN
--------------------	---

FLECAFIX 11/24

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

Example of use

