

RS 70
RF RS 70 RE/A3/M.BEZ**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The RS 70 profile is supplied in fixed lengths. The desired length is obtained by connecting the individual pieces together. The PCB is pushed into the side of the profile. End cover plates close off the sides of the profile.. Elements for terminal rails and direct mounting are available here. The clip-on feet are permanently attached to the profile. Marking options are integrated into the side pieces.

General ordering data

Type	RF RS 70 RE/A3/M.BEZ
Order No.	0119560000
Version	Clip-in foot, RS 70 Orange, Clip-in foot, Width: 10 mm
GTIN (EAN)	4008190087111
Qty.	20 pc(s).

RS 70
RF RS 70 RE/A3/M.BEZ

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	70 mm	Width	10 mm
Height	33.5 mm	Height of lowest version	32 mm
Net weight	6.154 g		

System characteristics

Version	Clip-in foot	Number of PCBs per module	1
PCB thickness	1.6 mm	Tolerance for the PCB shape	±0.2
Cross-connection	No	Contact to terminal rail	No
Protection degree	IP 20	Encapsulation option	No

Material data

UL 94 flammability rating	V-2	Insulating material	PA 66
Colour	Orange	Max. relative humidity during storage	93 %

Classifications

ETIM 3.0	EC001284	UNSPSC	30-21-18-01
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14

Approvals

Approvals	
ROHS	Conform