

## SAK Series, Accessories EP 2 SAKG46/35 HP/DBR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



To guarantee a finger-proof level of safety when using modular terminals, open sides are covered with end or partition plates to prevent contact with live parts.

### General ordering data

Type	EP 2 SAKG46/35 HP/DBR
Order No.	<a href="#">0180700000</a>
Version	SAK Series, Accessories, End plate, Dark brown, 2 mm
GTIN (EAN)	400819009967 1
Qty.	10 pc(s).

## SAK Series, Accessories EP 2 SAKG46/35 HP/DBR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	160 mm	Width	2 mm
Height	91 mm	Net weight	35.4 g

### Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Additional technical data

Version	End and intermediate plate
---------	----------------------------

### Dimensions

TS 32 offset	80 mm
--------------	-------

### Material data

Material	PA 66	Colour	Dark brown
UL 94 flammability rating	V-2		

### System specifications

Product family	SAK Series, Accessories	Mounting rail	TS 35
----------------	-------------------------	---------------	-------

### Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads

STEP	<a href="#">0180700000_09105_EP_2_SAKG46-35_HP-DBR_STP.stp</a>
------	--