

**Accessories  
PS 4 F.STB 4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The solution with Weidmüller test plugs and sockets guarantees a proper test of the installation.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | PS 4 F.STB 4               |
| Order No.  | <a href="#">0299600000</a> |
| Version    | Accessories, Test plug     |
| GTIN (EAN) | 4008190074043              |
| Qty.       | 20 pc(s).                  |

**Accessories  
PS 4 F.STB 4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

|            |        |                          |       |
|------------|--------|--------------------------|-------|
| Width      | 7.6 mm | Height of lowest version | 42 mm |
| Net weight | 3.16 g |                          |       |

**Temperatures**

|                       |                     |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

**Additional technical data**

|                     |                 |         |           |
|---------------------|-----------------|---------|-----------|
| Installation advice | Direct mounting | Version | Test plug |
|---------------------|-----------------|---------|-----------|

**Clampable wires (rated connection)**

|                    |                    |
|--------------------|--------------------|
| Type of connection | Plug-in connection |
|--------------------|--------------------|

**Material data**

|                           |              |        |     |
|---------------------------|--------------|--------|-----|
| Material                  | Polyamide 66 | Colour | Red |
| UL 94 flammability rating | V-2          |        |     |

**System specifications**

|                |             |                    |                    |
|----------------|-------------|--------------------|--------------------|
| Product family | Accessories | Type of connection | Plug-in connection |
|----------------|-------------|--------------------|--------------------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC002255    | UNSPSC     | 30-21-18-01 |
| eClass 6.2 | 27-14-92-14 | eClass 7.1 | 27-14-92-14 |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|      |   |
|------|---|
| DXF  | <a href="#">02965_PS_4_F.STB_4_DXF.dxf</a>    |
| STEP | <a href="#">0299600000_02965_PS_4_STP.stp</a> |