

**Accessories**  
**G 20/3.15A/F****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | G 20/3.15A/F               |
| Order No.  | <a href="#">0431100000</a> |
| Version    | Active components, Fuse    |
| GTIN (EAN) | 4008190012977              |
| Qty.       | 10 pc(s).                  |

## Data sheet

### Accessories G 20/3.15A/F

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 5 mm   | Width (inches)  | 0.197 inch |
| Height     | 20 mm  | Height (inches) | 0.787 inch |
| Depth      | 5 mm   | Depth (inches)  | 0.197 inch |
| Net weight | 1.08 g |                 |            |

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Material data

Colour Light Grey

### System specifications

Version Fuse accessories

### Fuse cartridges

|                         |                    |                         |                  |
|-------------------------|--------------------|-------------------------|------------------|
| Cartridge fuse          | G-Si. 5 x 20       | Characteristics         | quick-acting     |
| Colour                  | Light Grey         | Current                 | 3.15 A           |
| Melting integral        | 4 A <sup>2</sup> s | Power output (@ 1.5 In) | 2.2 W            |
| Rated breaking capacity | 1.5 kA             | Version                 | Fuse accessories |
| Voltage drop            | 220 mV             |                         |                  |

### Rating data

|               |       |               |        |
|---------------|-------|---------------|--------|
| Rated voltage | 250 V | Rated current | 3.15 A |
|---------------|-------|---------------|--------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000035    | ETIM 4.0   | EC000035    |
| ETIM 5.0   | EC000035    | ETIM 6.0   | EC000035    |
| UNSPSC     | 30-21-18-14 | eClass 5.1 | 27-14-20-07 |
| eClass 6.2 | 27-14-20-07 | eClass 7.1 | 27-14-20-90 |
| eClass 8.1 | 27-14-20-90 | eClass 9.0 | 27-14-20-01 |
| eClass 9.1 | 27-14-20-01 |            |             |

### Approvals

ROHS Conform

### Downloads

Brochure/Catalogue [CAT 1 TERM 16/17 EN](#)  
 Engineering Data [WSCAD](#)