

**Accessories**  
**G 25/0.80A/M GR****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | G 25/0.80A/M GR            |
| Order No.  | <a href="#">0646400000</a> |
| Version    | Active components, Fuse    |
| GTIN (EAN) | 4008190060794              |
| Qty.       | 10 pc(s).                  |

## Data sheet

### Accessories G 25/0.80A/M GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Width      | 5 mm  | Width (inches)  | 0.197 inch |
| Height     | 25 mm | Height (inches) | 0.984 inch |
| Depth      | 5 mm  | Depth (inches)  | 0.197 inch |
| Net weight | 1.2 g |                 |            |

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

### Material data

|        |            |
|--------|------------|
| Colour | Light Grey |
|--------|------------|

### System specifications

|         |                  |
|---------|------------------|
| Version | Fuse accessories |
|---------|------------------|

### Fuse cartridges

|                         |                  |                         |                      |
|-------------------------|------------------|-------------------------|----------------------|
| Cartridge fuse          | G-Si. 5 x 25     | Characteristics         | medium time-lag      |
| Colour                  | Light Grey       | Colour of the indicator | grey                 |
| Current                 | 0.8 A            | Melting integral        | 1.6 A <sup>2</sup> s |
| Power output (@ 1.5 In) | 0.2 W            | Rated breaking capacity | 1.5 kA               |
| Version                 | Fuse accessories | Voltage drop            | 400 mV               |

### Rating data

|               |       |               |       |
|---------------|-------|---------------|-------|
| Rated voltage | 250 V | Rated current | 0.8 A |
|---------------|-------|---------------|-------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000035    | ETIM 4.0   | EC000035    |
| ETIM 5.0   | EC000035    | ETIM 6.0   | EC000035    |
| UNSPSC     | 30-21-18-14 | eClass 5.1 | 27-14-20-07 |
| eClass 6.2 | 27-14-20-07 | eClass 7.1 | 27-14-20-90 |
| eClass 8.1 | 27-14-20-90 | eClass 9.0 | 27-14-20-01 |
| eClass 9.1 | 27-14-20-01 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                     |
|--------------------|-------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a> |
| Engineering Data   | <a href="#">WSCAD</a>               |