

## W-Series, Accessories WQV 70/95/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm<sup>2</sup> to 300 mm<sup>2</sup> - means that you have diverse options for your applications at your disposal. Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

### General ordering data

Type	WQV 70/95/3
Order No.	<a href="#">106360000</a>
Version	W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 3
GTIN (EAN)	4008190187514
Qty.	5 pc(s).

## W-Series, Accessories WQV 70/95/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	54 mm	Width	10 mm
Height	61.6 mm	Net weight	159.8 g

### Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

### Additional technical data

Explosion-tested version	No	Version	For the terminals
--------------------------	----	---------	-------------------

### Clampable wires (rated connection)

Tightening torque, max.	3 Nm
-------------------------	------

### Rated data

Rated current	232 A
---------------	-------

### Material data

Material	Steel	Colour	Grey
----------	-------	--------	------

### System specifications

Product family	W-Series, Accessories
----------------	-----------------------

### Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

### Approvals

ROHS	Conform
------	---------