

**OMNIMATE Housing - series CH20M
CH20M22 S PPSC GGY**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

**Superior efficiency, flexibility and design - the "standard tailor-made fit"**

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customised design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M22 modular electronics housing is the standard format from amongst the different housing widths. It has the optimal width for most typical electronics applications.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- **Quicker installation** with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- **Maximum interference immunity** with ESD-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular". CH20M also stands for efficiency and innovation throughout design, production and use.

General ordering data

Type	CH20M22 S PPSC GGY
Order No.	1073370000
Version	Electronics housings, OMNIMATE Housing - series CH20M Graphite grey, Side element, Width: 22.5 mm
GTIN (EAN)	4032248831173
Qty.	10 pc(s).

Datenblatt

**OMNIMATE Housing - series CH20M
CH20M22 S PPSC GGY**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	105.5 mm	Width	22.5 mm
Height	22.83 mm	Net weight	8.8 g

Material data

UL 94 flammability rating	V-0	Insulating material	PA 66 GF 30
Colour	Graphite grey		

Classifications

eClass 6.2	27-18-05-05	eClass 7.1	27-18-05-05
------------	-------------	------------	-------------

Approvals

Approvals	
ROHS	Conform

Datenblatt

**OMNIMATE Housing - series CH20M
CH20M22 S PPSC GGY**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

