

**OMNIMATE Housing - series CH20M  
CH20M12 B BK/OR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Superior efficiency, flexibility and design - the "standard tailor-made fit"**

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customized design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M12 modular electronics housing is the "small" option amongst the "large" housing solutions for compact electronics applications.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- **Quicker installation** with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- **Maximum interference immunity** with EMC-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular". CH20M also stands for efficiency and innovation throughout design, production and use.

**General ordering data**

Type	CH20M12 B BK/OR
Order No.	<a href="#">1104180000</a>
Version	Electronics housings, OMNIMATE Housing - series CH20M Black, Base element, Width: 12 mm
GTIN (EAN)	4032248878819
Qty.	14 pc(s).

## OMNIMATE Housing - series CH20M CH20M12 B BK/OR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	107.4 mm	Width	12 mm
Height	109.3 mm	Net weight	31.47 g

### System characteristics

Version	Base element	Type of connection	without
Number of PCBs per module	1	PCB thickness	1.6 mm
Tolerance for the PCB shape	±0.15 mm	Contact to terminal rail	No
Protection degree	IP 20	Encapsulation option	No

### Material data

UL 94 flammability rating	V-0	Insulating material	PA 66 GF 30
Colour	Black		

### Classifications

eClass 6.2	27-18-09-90	eClass 7.1	27-18-27-02
------------	-------------	------------	-------------

### Approvals

Approvals	
ROHS	Conform

**Datenblatt**

**OMNIMATE Housing - series CH20M  
CH20M12 B BK/OR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

