

Accessories
ETA 1170 21 25A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Spring connection with tension clamp Technology

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	ETA 1170 21 25A
Order No.	1278830000
Version	Accessories, Circuit breaker, 25 A
GTIN (EAN)	4050118091335
Qty.	5 pc(s).

Data sheet

Accessories ETA 1170 21 25A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	9.8 mm	Width (inches)	0.386 inch
Height	22 mm	Height (inches)	0.866 inch
Depth	51.6 mm	Depth (inches)	2.031 inch
Net weight	10.2 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Material data

Colour	black
--------	-------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Rating data

Rated voltage	28 V DC	Rated current	25 A
---------------	---------	---------------	------

Classifications

ETIM 6.0	EC000035	eClass 6.2	27-14-20-90
eClass 7.1	27-14-20-90	eClass 8.1	27-14-20-90
eClass 9.0	27-14-20-01	eClass 9.1	27-14-20-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
------------------	------------------------------