

**Clamping yoke
KLBUE 4-13.5 SC M4X16**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Shielding and earthing

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	KLBUE 4-13.5 SC M4X16
Order No.	1712311002
Version	Clamping yoke, Clamping yoke
GTIN (EAN)	4032248064403
Qty.	10 pc(s).

Clamping yoke KLBUE 4-13.5 SC M4X16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	2.1 mm	Width (inches)	0.083 inch
Height	22 mm	Height (inches)	0.866 inch
Depth	31.45 mm	Depth (inches)	1.238 inch
Net weight	19.2 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Colour	silver
--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of mounting	Screw		

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC002020
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-50
eClass 8.1	27-14-11-50	eClass 9.0	27-14-11-50
eClass 9.1	27-14-11-50		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
User Documentation	Beipackzettel_KLBUE.pdf