

WAVEBOX
WAVEBOX L 17.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

**Do not use product for new
developments**



Modular electronics housing, 17.5 mm wide with 4 No.
 3-pole 2-tier plug-in connections (screw and tension
 clamp). Height of enclosure: 112 mm

General ordering data

Delivery status	This article will no longer be available in the future.
Available until	2019-12-31
Type	WAVEBOX L 17.5
Order No.	8426560000
Version	Electronics housings, WAVEBOX Pebble grey, Housing base part, Width: 17.5 mm
GTIN (EAN)	4032248037667
Qty.	10 pc(s).

WAVEBOX WAVEBOX L 17.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	92.4 mm	Length (inches)	3.638 inch
Width	17.5 mm	Width (inches)	0.689 inch
Height	112.4 mm	Height (inches)	4.425 inch
Net weight	47.5 g		

System characteristics

Version	Housing base part	Number of PCBs per module	1
PCB thickness	1 mm	Type of contact to PCB	Solder connection, direct
Tolerance for the PCB shape	±0.1 mm	Cross-connection	No
Contact to terminal rail	No	Protection degree	IP20
Max. power loss	2 W		

Material data

Colour	Pebble grey	Colour chart (similar)	RAL 7032
CTI	≥ 175	UL 94 flammability rating	V-0
Storage temperature, min.	-25 °C	Storage temperature, max.	55 °C
Max. relative humidity during storage	80 %	Operating temperature, min.	-50 °C
Temperature range, installation, min.	-25 °C		

Classifications

ETIM 3.0	EC001284	ETIM 5.0	EC001031
ETIM 6.0	EC001031	UNSPSC	30-21-18-01
eClass 6.2	27-18-08-02	eClass 7.1	27-18-27-02
eClass 8.1	27-18-27-02	eClass 9.0	27-18-27-90
eClass 9.1	27-18-27-90		

Notes

Notes

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [FL ANALO.SIGN.CONV. EN](#)
[MB DEVICE MANUF. EN](#)
[FL MACHINE SAFETY EN](#)
[FL 72H SAMPLE SER EN](#)
[PO OMNIMATE EN](#)