

European Region

634495

European Region



BRIGHT

- Four White LEDs provide 55 lumens of light in high mode



ECONOMICAL

- Provides useable light in high mode for 29 hours with Energizer® MAX® batteries
- Low mode provides light for 58 hours



WATERPROOF

- Meets IEC 60529 IPX7 standards
- Continues to operate after submersion in 1 meter of water for 30 minutes



FLOATS

- Easy recovery from water
- Great for boating



BENEFITS

- 360° lighting
- Stands on base or hangs using integrated hook
- Cushioned handle for comfortable carrying
- Easy to use push-button switch
- Three lighting modes – high, low and Amber nightlight

Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light


Product Detail:

Designation: Energizer
Camping Lantern
SAP: 634495
Colour: Green
Power Source: Three "AA"
IEC: LR6
Lamp: Four White LEDs, One Amber LED
Lamp Life (hr): Lifetime

Mode:	High	Low
Light Output (lumens):	55	28
Run Time (h:min):	29	58

Typical Weight (g): 437
without batteries
Dimensions (mm): 184 x 107

Performance:



Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved