




4RCC



Part No	Inductance (μ H)	fL (MHz)	Tol \pm (%)	Rated DC Current (A)	Temp. rise Δ ($^{\circ}$ C)	ISAT (A)	DCR (Ω)	Dimensions					
								\varnothing d	\varnothing D1	(A)	\varnothing D	F	F1
4RCC-1R8M-00	1.8	1	20	10	< 15	15.0	0.003	1.32	4.0	20	6.9	15.9	5.4
4RCC-4R7M-00	4.7	1	20	6	< 15	8.2	0.007	1.00	4.0	25	6.3	18.4	5.1
4RCC-7R0M-00	7.0	1	20	5	< 15	6.5	0.008	0.95	4.0	30	6.2	19.5	5.0
4RCC-9R0M-00	9.0	1	20	4	< 15	5.6	0.015	0.85	4.0	30	6.0	20.1	4.9
4RCC-120M-00	12.0	0.1	20	2	< 15	5.0	0.022	0.63	4.0	25	5.5	16.9	4.7

Material : Ferrite

Revised : 06 Jul 10

SPQ : Loose / Box 1000 [-00]

All dimensions in mm

Rod Core Chokes