




LSSC



Typical |Z| vs Frequency(f)



| Part No | Inductance L (μH) | f _L (MHz) | Tol ± (%) | DCR max (mΩ) | Rated DC Current (A) | Ø d (mm) |
|--------------|-------------------|----------------------|-----------|--------------|----------------------|----------|
| LSSC-5R0M-00 | 5 | 1 | 20 | 5 | 10 | 1.3 |
| LSSC-9R0M-00 | 9 | 1 | 20 | 12 | 6 | 0.95 |
| LSSC-150M-00 | 15 | 0.1 | 20 | 24 | 4 | 0.75 |
| LSSC-250M-00 | 25 | 0.1 | 20 | 46 | 3 | 0.63 |

Material : Ferrite

Remark : Available also without insulating material (LSSC/B)

SPQ :

| Packing Form | Loose / Box |
|--------------|-------------|
| Axial | 200 [-00] |

All dimensions in mm

Suppression Coils