




SMD BEADS

Flat Wire For High Currents



SMB/001




Typical Z vs Frequency



SMB/002



Typical Z vs Frequency



Wide Band Chokes

Part No	Impedance Z (Ω Typ)		DCR max (Ω)	Rated DC Current max (A)
	56ΩTyp @ 100MHz	63Typ @ 300MHz		
SMB/001-999X-01	56ΩTyp @ 100MHz	63Typ @ 300MHz	0.01	5
SMB/002-999X-01	100ΩTyp @ 100MHz	112Typ @ 300MHz	0.015	5

Material : Ferrite

SPQ :

Reel
500 [-01]
3000 [-04]