




**MOTOR CAPACITORS
SERIES WB 40.....**

Datum: 19.01.16



L = 51mm B = 35mm
D = 25mm C = 10mm
A = 350mm

	Modell	ECOFILL WB 40 - 30/B
1	Dielectric	METALLIZED POLYPROPYLENE
2	Filling	RESIN
3	Case material	Thermoplastic Self-Estinguish V2" Class
4	Capacitance / Tolerance	3 µF ±5%
5	Rated frequency	50 Hz – 60 Hz
6	Rated voltage	a) AC 400 V 1 µF50 µF b) AC 450 V 1 µF25 µF
7	Type of operation	DB
8	Life expectanca	a) B b)C
9	Class of operation	a) 10.000 h b) 3.000 h
10	Climatic Category	40/085/21
11	Class of safety protection	P0
12	Test Voltage between terminals	2,15 U _N x 2"
13	Test Voltage between terminals to case	2.500 V x 2"
14	Insulating Resistance between terminals	10 x 10 ³ MΩ x µF
15	Tan δ	<=5 x 10 ⁻⁴
16	DV/dt (typical)	10 V/µs
17	Tested and Certified according to	EN 60252-1 : 2011
18	Certification marks	VDE