

## Cable housing - KGG-MC 1,5/10 - 1834424

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable housing, Pitch: 3.81 mm, Number of positions: 10, Dimension a: 40.49 mm, Color: green

### Product Features

- For MC or IMC plugs with and without flange, and 3.81 mm pitch
- Straight cable outlet for sequencing several cable housings
- Incl. cable binders and marker strips for any numbers of positions
- Incl. transparent label carriers from 6- to 16-pos.
- Easier plug-in and disconnection processes
- Strain relief for the cables provided by cable binder or a clamp
- Full latching of both half shells of the cable housing

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4017918110765

### Technical data

#### Dimensions

<b>Height</b>	45.6 mm
<b>Width</b>	14.5 mm
<b>Pitch</b>	3.81 mm
<b>Dimension a</b>	40.49 mm

#### General

<b>Range of articles</b>	KGG-MC 1,5
<b>Insulating material group</b>	I
<b>Insulating material</b>	ABS
<b>Inflammability class according to UL 94</b>	HB
<b>Number of positions</b>	10

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	272607xx
<b>eCl@ss 4.1</b>	27260701

# Cable housing - KGG-MC 1,5/10 - 1834424

## classifications

### eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000879
ETIM 5.0	EC000451


### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## approvals

GOST / GOST /

### Approval details



## accessories

### Terminal marking

SBS10:UNBEDRUCKT - 1007248



# Cable housing - KGG-MC 1,5/10 - 1834424

accessories

KGG-MC 1,5/ DST - 1839050



## Drawings

Dimensioned drawing

