

Electronic housing - EMG 17-LG/SET - 2942988

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Electronic housing set, consisting of electronic housing and printed circuit termination blocks, pitch 5

Product Features

- Choice of four cover sizes in transparent or color versions
- Practical and easy-to-wire conductor connections
- High degree of flexibility due to the wide choice of versions
- Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- Uniform and appropriate housing technology
- User-friendly and safe mounting on DIN rails according to EN 60715
- Inflammability class V0 insulation material (according to UL 94)
- Shock and contamination-proof accommodation of electronic components
- Universal PCBs for all pitches

Key commercial data

package_quantity	10
GTIN	4017918080945

Technical data

General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color	green

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
--	-------------------

Dimensions

Length	75 mm
Constructional height	47.5 mm
Width	17.5 mm
Pitch	5 mm

Technical data

Inflammability class according to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	1.3 W 1.4 W 7.5 mm

Electronic housing - EMG 17-LG/SET - 2942988

Technical data

Technical data

Power dissipation at 20°C in the horizontal mounting position	1.5 W 1.6 W 15 mm
Power dissipation at 20°C in the horizontal mounting position	2.1 W 2.7 W 35 mm
Power dissipation at 20°C in the horizontal mounting position	2.7 W 4 W 52 mm
Number of positions	6

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

accessories

Filler plug

EMG-KA - 2941510



PCB

Electronic housing - EMG 17-LG/SET - 2942988

accessories

P 1-EMG 17 - 2946120



accessories

EMG-GKS 12 - 2947035




EMG-SGKS 10 - 2947585



Drawings


Electronic housing - EMG 17-LG/SET - 2942988

Dimensioned drawing



1 = Top edge of the PCB B = Housing width

Dimensioned drawing



Pitch 5 mma = Area for mounting components, 38 mm in the hood
Area for mounting components, 45 mm in the housing

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>