


C0603C334K4RACTU

aka C0603C334K4RAC7867

Capacitor, ceramic, 0.33 uF, +/-10% Tol, 16V, X7R, 0603



Dimensions (mm)

Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	1.60	+/-0.15	Capacitance:	0.33 uF
W	0.80	+/-0.15	Chip Size:	0603
T	0.8	+/-0.07	Voltage:	16V
B	.35	+/-0.15	Temperature Coefficient:	X7R
S	0.7	min	Tolerance:	+/-10%
			Application:	Std Chip
			Termination Type:	Tin
			Marked:	No
			Dissipation Factor:	3.5%
			Insulation Resistance:	1.52 GOhm
			Dielectric Strength:	40V
			Package Kind:	T&R
			Package Size:	7in
			Package Type:	Paper Tape
			Package Quantity:	4000