


# C0805C102J5GACTU

aka C0805C102J5GAC7867

Capacitor, ceramic, 1000 pF, +/-5% Tol, 50V, C0G, 0805



## Dimensions (mm)

## Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	2.00	+/-0.20	Capacitance:	1000 pF
W	1.25	+/-0.20	Chip Size:	0805
T	0.78	+/-0.1	Voltage:	50V
B	0.50	+/-0.25	Temperature Coefficient:	C0G
S	0.75	min	Tolerance:	+/-5%
			Application:	Std Chip
			Termination Type:	Tin
			Marked:	No
			Dissipation Factor:	0.1%
			Insulation Resistance:	100 GOhm
			Dielectric Strength:	125V
			Package Kind:	T&R
			Package Size:	7in
			Package Type:	Paper Tape
			Package Quantity:	4000