


C1206C103K5RACTU

aka C1206C103K5RAC7800

Capacitor, ceramic, 0.01 uF, +/-10% Tol, 50V, X7R, 1206



Dimensions (mm)

Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	3.20	+/-0.20	Capacitance:	0.01 uF
W	1.60	+/-0.20	Chip Size:	1206
T	0.78	+/-0.1	Voltage:	50V
B	0.50	+/-0.25	Temperature Coefficient:	X7R
			Tolerance:	+/-10%
			Application:	Std Chip
			Termination Type:	Tin
			Marked:	No
			Dissipation Factor:	2.5%
			Insulation Resistance:	100 GOhm
			Dielectric Strength:	125V
			Miscellaneous Electrical:	Note: Kemet 50 Volt parts may be operated afor 63 volt applicaitons
			Package Kind:	T&R
			Package Size:	7in
			Package Type:	Plastic Tape
			Package Quantity:	4000