


Electromagnets

Electromagnets



Sealed


Heavy duty

Strong

ITS-MS 4027

M

Type



Force-stroke-diagram (N/mm)

Description

Weight: 230 g

Power: 6,0 Watt

Holdingforce: 200 N

Mounting plates (minimum): 4,5 mm

Dimension

a	b	c	d	e
40	27	26	6	M3/M5

Solenoid Layout

Voltage Rating:

12 VDC (standard)

24 VDC (standard)

Special development

Do you like a costum designed version (for example frame, force, duty cycle and so on) please send us this form:

[Checklist \(PDF, 390 kB\)](#)