


Item no.: 286-375
 Product description: Relay module Relay with 4 changeover contacts (4u)



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	6 (Electronics)
Coil voltage DC	24 V
max. make current	2 A
max. break current	4 A
Max. continuous current	AC/DC 4 A
max. switching power (resistive) W	60 W
max. switching power (resistive) VA	1000 VA
Pull-in power	500 mW
Operating power	770 mW
Pull-in time (typ)	6 ms
Drop-out time (typ)	7 ms
Bounce time (typ)	2 ms
Dielectric strength contact-coil (AC, 1 min)	1.5 kV
Nominal voltage acc. to VDE 0110/1.89	250 V / 4 kV / 3
Mechanical life	5 x 10 ⁷ switching operations
Mechanical life at max. resistive load AC	1 x 10 ⁵ switching operations
Ambient operating temperature	-25 °C ... +40 °C
Current consumption at UN (20 °C)	32 mA
Weight	58.5 g

Color
Country of Origin

grey
Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected