



Data Sheet

NdFeB-Magnet Ring N35M



Dimension

Item no.	Outer Ø (A)	Inner Ø (B)	Height (C)
506015	10mm	5mm	10mm
506017	10mm	5mm	5mm
506018 / 1570148	10mm	5mm	2mm
506019	20mm	10mm	10mm
506022 / 1566722	20mm	10mm	5mm
506023	20mm	10mm	2mm

Data Sheet

Grade	N35M
Remanence Br	11.8 to 12.4 kGs
Coercivity bHc	≥ 10.9 kOe
Intrinsic Coercivity iHc	≥ 14 kOe
Max Energy Product BHmax	33 to 37 MGOe
Operating Temperature	max. 100°C
Tolerance	± 0.1 mm