



Data Sheet

NdFeB-Magnet Ring N35EH



Dimension

Item no.	Outer Ø (A)	Inner Ø (B)	Height (C)
506024	10mm	5mm	10mm
506025	10mm	5mm	5mm
506026 / 1566723	10mm	5mm	2mm
506027	20mm	10mm	10mm
506029	20mm	10mm	5mm
506030	20mm	10mm	2mm

Data Sheet

Grade	N35EH
Remanence Br	11.8 to 12 kGs
Coercivity bHc	≥11.2 kOe
Intrinsic Coercivity iHc	≥30 kOe
Max Energy Product BHmax	33 to 36 MGOe
Operating Temperature	max. 200°C
Tolerance	±0.1mm