


Data Sheet

NdFeB-Magnet Disc N35



Dimension

Item no.	Ø (A)	Height (B)
506102	2mm	10mm
505777 / 1572111	2mm	5mm
505780 / 1566704	2mm	2mm

Data Sheet

505782 / 1565123	5mm	20mm
505783 / 1566705	5mm	10mm
505784 / 1570140	5mm	5mm
505785 / 1572112	5mm	2mm
505788 / 1572113	10mm	10mm
505789 / 1566706	10mm	5mm
505791 / 1571352	10mm	2mm
505796 / 1570141	20mm	10mm
505797 / 1565124	20mm	5mm
505798 / 1570142	20mm	2mm

Grade	N35
Remanence Br	11.8 to 12.4 kGs
Coercivity bHc	≥10.9 kOe
Intrinsic Coercivity iHc	≥12 kOe
Max Energy Product BHmax	33 to 37 MGOe
Operating Temperature	max. 80°C
Tolerance	±0.1mm