


Surface probe (cross-band) with thread Type 18 NiCr-Ni

Product-Data	
Sensor element:	Type K NiCr-Ni Classe 2
Temperature range:	-50...+180 °C
Cross band	M12 x 1 Nickel-plated
Connecting cable:	Silicone insulated Ø 4 mm / 2 x 0.25 mm ²
Connecting cable length:	2 meters
Tmax connecting cable:	+ 180 °C
Plug:	open wire ends
Accuracy:	DIN IEC 60584 Class B
Order-Information	
TSG-Order-Number:	8006 1324
Conrad-Order-Number:	50 77 98-XX

Dimensioning



Photograph



example of installation

