


Magnetic Surface Probe (cross band) with PTFE handle Type 19 NiCr-Ni Type K

Product-Data	
Sensor element:	Type K NiCr-Ni Class 2
Temperature range:	-50...+180 °C
Installation length:	37 mm
Probe tube material:	PTFE handle
Cross-band:	10 x 30 mm
Cross-band material:	Stainless steel 1.4305
Connecting cable:	Shielded Silicone extension cable Ø 4 mm / 2 x 0.22 mm ²
Connecting cable length:	2 meters
Tmax connecting cable:	+180 °C
Plug:	open wire ends
Accuracy:	Class 2 DIN IEC 60584 Class 2
Order-Information	
TSG-Order-Number:	8006 1325
Conrad-Order-Number:	50 78 00-XX

Dimensions	
	
Picture	example of installation
