

## Ambient temperature Probe (Outdoor) Type 20 F50 Pt 100


### Product-Data

Sensor element:	Pt 100 Class B
Temperature range:	-50...+80 °C
Housing:	82 x 55 x 33 mm
Connecting cable:	PVC insulated Ø 4.5 mm / 4 x 0.14 mm <sup>2</sup>
Connecting cable length:	2 meters
Tmax connecting cable:	+80 °C
Plug:	Open wire ends
Accuracy	Class B DIN IEC 60751 +/- 0.3 °C

### Order-Information

TSG-Order-Number:	8006 1426
Conrad-Order-Number:	50 78 01-XX

### Dimensions



### Picture

